


Blow-off cabinet CABK 1000 PS

Artikel-Nr. 7815-S

Pretreated surfaces have proven their worth in tool coating, as they are an important prerequisite for coating quality! The CABK 1000 blow-off cabinet is used to remove adhering residual particles after blasting.

- For manual blowing-off of the tools
- Large opening sliding door
- Spaciously dimensioned blow-off chamber
- Extraction with integrated filter technology

Experten kontaktieren

 +49 2405 44 70 122

 coatingtechnology@cemecon.de



Technische Daten

Process step	radiate
Coating procedure	Follow up treatment Pretreatment
Type	CABK 1000 PS
Net weight	330 kg
measurement (LxWxH)	1260 x 1700 x 2060 mm Dimensions blow-off chamber: 990 x 800 x 710 mm
Connector	400V/50Hz; 3 Ph+N+PE
Connected Load (KW)	<1
Ampere	16 A

The CABK1000 blow-off cabinet is part of our CSA 1000 S4 blasting line. It has a large-volume blow-off chamber, which is loaded through a wide-opening sliding door. The molds are then blown off manually. The dust is extracted by the recirculation system via a long-life filter cartridge. Since a secondary filter is used, connection to an exhaust air system is not necessary.